

Device	Pin Cnt	Clock Speed	Flash	RAM	EEPROM	Digi Pins	CAN Pins	I2C Pins	SPI Pins	UART Pins	USB Pins	PWM
Arduino BT 168	32	16000000	16384	1024	512	21	0	1	1	1	0	6
Arduino BT 328	32	16000000	32768	2048	1024	21	0	1	1	1	0	6
Arduino Duemilanove 168	28	16000000	16384	1024	512	23	0	1	1	1	0	6
Arduino Duemilanove 328P	28	16000000	32768	2048	1024	23	0	1	1	1	0	6
Arduino Duemilanove168P	28	16000000	16384	1024	512	23	0	1	1	1	0	6
Arduino EtherTen	32	16000000	32768	2048	1024	21	0	1	1	1	0	6
Arduino Ethernet	32	16000000	32768	2048	1024	21	0	1	1	1	0	6
Arduino Fio	32	8000000	32768	2048	1024	21	0	1	1	1	0	6
Arduino Leonardo	44	16000000	32768	2560	1024	26	0	1	1	1	1	9
Arduino LilyPad 168	32	8000000	16384	1024	512	21	0	1	1	1	0	6
Arduino LilyPad 328	32	8000000	32768	2048	1024	21	0	1	1	1	0	6
Arduino LilyPad SSS	32	8000000	32768	2048	1024	11	0	1	1	1	0	6
Arduino LilyPad Usb	44	16000000	32768	2560	1024	26	0	1	1	1	0	8
Arduino Mega 1280	100	16000000	131072	8192	4096	86	0	1	1	2	0	16
Arduino Mega 2560 R3	100	16000000	262144	8192	4096	86	0	1	1	4	0	16
Arduino Mega 2560	100	16000000	262144	8192	4096	86	0	1	1	4	0	16
Arduino Mega ADK 2560 R3	100	16000000	262144	8192	4096	86	0	1	1	4	0	16
Arduino Mega ADK 2560	100	16000000	262144	8192	4096	86	0	1	1	4	0	16
Arduino Micro 8MHz	44	8000000	32768	2560	1024	26	0	1	1	1	1	8
Arduino Micro	44	16000000	32768	2560	1024	26	0	1	1	1	1	8
Arduino Mini	32	16000000	32768	2048	1024	21	0	1	1	1	0	6
Arduino Nano 168	32	16000000	16384	1024	512	21	0	1	1	1	0	6
Arduino Nano 328 115200	32	16000000	32768	2048	1024	21	0	1	1	1	0	6
Arduino Nano 328	32	16000000	32768	2048	1024	21	0	1	1	1	0	6
Arduino Pro 168 3V3	32	8000000	16384	1024	512	21	0	1	1	1	0	6
Arduino Pro 168 5V	32	16000000	16384	1024	512	21	0	1	1	1	0	6
Arduino Pro 328 3V3	32	16000000	32768	2048	1024	21	0	1	1	1	0	6
Arduino Pro 328 5V	32	16000000	32768	2048	1024	21	0	1	1	1	0	6
Arduino Pro Mini 3V3	32	8000000	16384	1024	512	21	0	1	1	1	0	6
Arduino Pro Mini 5V	32	16000000	16384	1024	512	21	0	1	1	1	0	6
Arduino RFu-328	20	16000000	32768	2048	1024	17	0	1	1	1	0	6
Arduino Trinket	8	20000000	8192	512	512	6	0	1	1	0	0	4

Arduino Uno PDIP	28	16000000	32768	2048	1024	23	0	1	1	1	0	6
Arduino Uno R3 PDIP	28	16000000	32768	2048	1024	23	0	1	1	1	0	6
Arduino Uno R3 SMD	28	16000000	32768	2048	1024	23	0	1	1	1	0	6
Arduino Uno SMD	28	16000000	32768	2048	1024	23	0	1	1	1	0	6
Arduino XinoRF	32	16000000	32768	2048	1024	21	0	1	1	1	0	6
Arduino Yun	44	16000000	32768	2560	1024	26	0	1	1	1	1	9
BL0055	28	16000000	32768	2048	1024	23	0	1	1	1	0	6